



Division of  
Acorn Engineering Company®



A MEMBER OF



Use



# S Series 85 Gallon Stationary Whirlpool

**S-85-S**



S-85-S

**Whitehall S-85-S Stationary Whirlpool** is recommended for treatment and prevention of sports injuries allowing coverage of the extremities, hips and back area. Professional, college and high school athletic trainers find the larger design most suitable when treating today's athletes.

**Tank Capacity** is 85 gallons.

**Whirlpool Tank** is 48"L x 20"W x 25"D and is seamless welded construction, fabricated from heavy gauge, type 304 stainless steel, polished to a satin finish. Tank rim is reinforced with a concealed stainless steel rod. Tank bottom is seamless, coved (rounded) design for effective cleaning to minimize bacteria buildup. Tank is also provided with an extended stainless steel skirt flush to the floor line to conceal internal drain piping.

A 2" Combination Drain and Overflow, and a Filler Spout are provided.

**Turbine Raising and Lowering Device** permits adjustment of desired height and direction of water agitation towards the area of the body to be treated. It is spring balanced and provided with a locking device.

**Turbine Assembly** is equipped with Underwriters Laboratory listed 1/2 HP jet pump motor protected with an ABS plastic shell, automatic thermal overload protector, and lifetime-sealed bearings. All parts contacting the water are stainless steel, chrome plated brass or bronze.

**Thermometer** is provided with a dual scale, adjustable calibration, and a stem inserts into a retainer to prevent rattle during whirlpool agitation.

### GUIDE SPECIFICATIONS

Provide Whitehall Stationary Whirlpool (specify model number and options) with a 85-gallon capacity, 48"L x 20"W x 25"D. Whirlpool shall be fabricated from heavy gauge, type 304 stainless steel. Construction shall be seamless welded and exposed surfaces shall be polished to satin finish. Tank shall have a reinforced rim and shall be fitted with a stainless steel skirt flush to the floor line. Bottom of tank shall be a seamless, rounded coved design to minimize bacteria build up. Provide a 2" combination drain and overflow, and a filler spout. Provide a turbine assembly with raising and lowering device which functions as an agitator and permits adjustment of desired height, direction of water agitation, and can be locked into place. Turbine assembly shall be UL listed 1/2 HP jet pump motor with automatic thermal overload protector and lifetime-sealed bearings. Provide a thermometer with a stem retainer to prevent rattle when whirlpool is in operation.

Please visit [www.whitehallmfg.com](http://www.whitehallmfg.com)  
for most current specifications.



Member of  
U.S. Green  
Building  
Council



Recyclable  
Product



### MODEL NUMBER AND OPTION SELECTIONS

#### Series

S Sports Series

#### Capacity

-85 Gallons

#### Type

-S Stationary Whirlpool

#### Turbine Electrical Requirements

115VAC / 50Hz       115VAC / 60Hz  
 230VAC / 50Hz       230VAC / 60Hz

Country of Use \_\_\_\_\_

#### For Mixing Valve:

Refer to supplemental MXT15 sheet for details.

#### Suffix Options (See Whirlpool Options Section for Details)

- AHC1 Adjustable High Chair with Casters
- AHC2 Adjustable High Chair with Rubber Tips
- ARS Arm Rest Support
- AS1 Adjustable Suspension Seat
- CTS1 Combination Table with Side Seats
- EG Enviro Glaze Color Powder Coating - Specify Color: \_\_\_\_\_  
(Special Finishes Consult Factory)
- GFI Ground Fault Interrupter
- PCS Pump Strainer Cover
- PHS2 Patient Handling System (Chair Type)
- RHG Rubber Hand Grips
- SDO Separate Drain and Overflow Assembly
- TTS1 Tank Top Seat

<b>ELECTRIC REQUIREMENTS:</b> Amps: 6.9/6.2 Hertz: 50/60 Volts: 115 GFI Receptacle	<b>ELECTRIC REQUIREMENTS:</b> Amps: 3.5/3.1 Hertz: 50/60 Volts: 230 GFI Receptacle	Certified per US & Canadian Medical Standards; UL 60601-1 & CSA C22.2 No. 601.1	Certified per European Standards; IEC 60601-1
--	--	--	---

CSA C22.2 No. 60601-1

**STATIONARY S-85-S SERIES WHIRLPOOL**

**NOTES:**

1. 1/2 HP Jet Pump Motor	5. Combination Drain & Overflow Assembly	9. 3 Pole GFI Receptacle by Others
2. Variable Pressure Control	6. "L" Brackets - (4) Four Each	10. Floor Drain by Others
3. Thermometer	7. Stainless Steel Tank	11. Filler Spout
4. Turbine Raising & Lowering Device	8. 2" O.D. x 5" Tailpiece	12. Mixing Valve, Shown For Reference Only

**WARNING:** Cancer and Reproductive Harm - [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

### SELECTION SUMMARY & APPROVAL FOR MANUFACTURING

Model Number & Options \_\_\_\_\_ Quantity \_\_\_\_\_  
 Company \_\_\_\_\_ Date \_\_\_\_\_  
 Contact \_\_\_\_\_ Title \_\_\_\_\_  
 Approval for Manufacturing/Signature \_\_\_\_\_

All dimensions are nominal and subject to manufacturer's change without notice. Whitehall assumes no responsibility for use of void or superseded data © Whitehall Manufacturing, Member of Morris Group International. Please visit [www.whitehallmfg.com](http://www.whitehallmfg.com) for most current specifications.